



15L Professional Quick Removing Dust Digital Ultrasonic Cleaner For Cell Phone

Our Product Introduction

Basic Information

- Place of Origin: ShenZhen
- Brand Name: SkyMen
- Certification: CE,RHOS
- Model Number: JP-060T
- Minimum Order Quantity: 1set
- Price: Negotiation
- Packaging Details: 1pcs / carton 1x ultrasonic cleaner 1x basket 1x lid 1x user manual
- Delivery Time: In Stock
- Payment Terms: T/T, Paypal
- Supply Ability: 500sets



Product Specification

- Model: JP-060T
- Tank Capacity: 15L
- Tank Size: 330*300*150mm
- Unit Size: 387*325*280mm
- Package Size: 460*410*360 Mm
- Frequency: 40KHz
- Power: 120/240W
- Heating Power: 300W
- Heater: Normal ~80C Adjustable
- Timer: 1~30min Adjustable
- Warranty Time: 1 Year
- Lead Time: Immediately After Payment
- Highlight: stainless steel ultrasonic cleaner, ultrasonic bath cleaner



More Images



for more products please visit us on skymenultrasonic.com

Product Description

15L Professional Quick Removing Dust Digital Ultrasonic Cleaner For Cell Phone

Application

1. What can you do on cellphone with ultrasonic cleaner?

Cell Phone PCB cleang:

As with many electronic devices, the printed circuit boards (PCBs) on today's mobile phones carry powerful functionality in a delicate setting. For those users who understand how to uninstall and replace their PCBs, they can remove the circuit boards and place them in a tray within the ultrasonic cleaner. As the PCBs are suspended in the detergent solution, the cavitation effect can remove any internal contaminants while preserving the electronic connections.

Water damage Treatment:

While some users make the mistake of trying to fix water-damaged phones themselves either by charging the phone or using a hot blow-dryer on the PCBs, ultrasonic cleaners are highly effective at remedying water damage to mobile phones. The process involves cleaning PCBs with a free-rinsing aqueous detergent solution, then rinsing with distilled water to remove any chemical residue. The PCBs are left to air-dry, as hot air from hair dryers can exacerbate the damage. Isopropyl alcohol can be used as a final rinse to accelerate the drying process.

Cell Phone Casing

Ultrasonic cleaners are just as effective at cleaning the casing on the outside of the phone as they are at cleansing the circuit boards on the inside. Mobile phone users can disassemble their phones and wash their casings in a special cleaning solution that can reach the smallest crevices. The sensitive input and display devices, such as the alphabet keys (for Blackberry-style smartphones) and the faceplate (for iPhone and Android-style models), will also remain undamaged.

Killing Bacteria and viruses:

Due to their constant use, mobile phones can also serve as a home for various disease-carrying microorganisms. For many years, physicians, dentists and other medical professionals have used ultrasonic cleaners as part of the process of cleaning and sterilizing their equipment. Mobile phone users can also use their ultrasonic cleaners to remove many of the bacteria and viruses that can cling to the surfaces of their phones.

How It Work

2.How ultrasonic cleaner work?

An electronic transducer, similar to those found in stereo speakers and amplifiers, is attached to a vibration-resistant metal tank. When the user fills the tank with water and cleaning solution, the transducer produces high-frequency sound waves that agitate the water, forming millions of microscopic bubbles. These bubbles reach into the narrow crevices and tiny holes that hand-cleaning methods can't touch. When the bubbles implode (a process called "cavitation"), they loosen and carry off the contaminating particles.

3.Drainage

15L ultrasonic cleaner is too heavy to pull out water by carrying whole machine up. So we have designed a drainage for you.

4.Specidication of JP-060T

Model	JP-060T	Frequency	40,000Hz
Tank capacity	15L	Timer	1-30 mins
Tank size	330*300*150mm	Unit size	387*325*280mm
Box packing	460*410*360 mm	Function	Degasing/Draining
Ultrasonic power	360W	Heating power	300W
N.W.	9.1kg	G.W.	10.3kg
POWER SUPPLY	AC 100 ~ 120V, 60Hz ; AC 220 ~ 240V, 50Hz		

5. Other Recommendation

If tank size is not suitable for your spare parts, we have other big ultrasonic cleaner in store. And we can design and produce any special function ultrasonic cleaning machine you need.

6.Packing information and delivery



7.SkyMen Advantage

We have been in this industry for 10 years and we are supplying machines to all seller all over the world.All distributor is

welcome for win-win cooperation.

We have passed ISO, High Tech Company, CE, RoHS, FCC, National Medical Instrument Approval.

8. Customers' feedback with skymen cleaning machine

<https://www.youtube.com/watch?v=-VMzEqOlaXE>

https://www.youtube.com/watch?v=cut8_HKLud8

Youtube: <https://www.youtube.com/watch?v=zjlppdkpLFw>

Youtube: <https://www.youtube.com/watch?v=oTHSCRt1H7Y&feature=youtu.be>



Skymen Technology Corporation Limited



86-755-27094405



info@skymen.cc



skymenultrasonic.com

Floor 1st & 2nd, Building 3, Tanggang Taifeng Industrial Park, Dawangshan Community, Shajing Street, Bao'an District, Shenzhen